

Hexagon head bolt MF DIN 960 Steel Plain 8.8 M10X1,25X80



Article number	01060.100.080
Brand	-
UBB	950351127473
UNSPSC	31161620
EAN	8715492019721
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
DIN	960
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	80
P	1.25
s	17

Technical Drawing

