



Hexagon head bolt MF DIN 960 Steel Plain 8.8 M12X1,50X90

Article number	01060.120.090
Brand	-
UBB	950351128612
UNSPSC	31161620
EAN	8715492019905
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
DIN	960
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	90
P	1.5
s	19

Technical Drawing

