

## Hexagon head bolt MEF DIN 960 Steel Plain 8.8 M18X1,50X120



Article number	01061.180.120
Brand	-
UBB	950351133158
UNSPSC	31161620
EAN	8715492020895
PKG. of 25	Full Box Only

### Technical Parameters

Diameter (d-D)	M18
Length (L) (mm)	120
P	1.50
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

### Standards

DIN	960
ISO	8765
NF	E25-152

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	48
b (min.): $L > 200\text{mm}$	61
b (min.): $L \leq 125\text{mm}$	42
k	11.5
s	27

### Technical Drawing

