



Hexagon head bolt MEF DIN 960 Steel Plain 8.8 M20X1,50X130

Article number	01061.200.130
Brand	-
UBB	952351326360
UNSPSC	31161620
EAN	8715492021076
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M20
Length	130 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric extra fine thread

Standards

NF	E25-152
NEN	1555
DIN	960
ISO	8765

Technical Specification

b (min.): 125mmL≤200mm	52
b (min.): L200mm	65
b (min.): L≤125mm	46
d-D	M20
k	12.5
L (mm)	130
P	1.5
s	30

Technical Drawing

