



Hexagon head bolt MF DIN 960 Steel Zinc plated 8.8 M12X1,50X120

Article number	01062.120.120
Brand	-
UBB	500648073608
UNSPSC	31161620
EAN	8717077201293
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
NEN	1555
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	120
P	1.5
s	19

Technical Drawing

