



Hexagon head bolt MF DIN 960 Steel Zinc plated 8.8 M14X1,50X65

Article number	01062.140.065
Brand	-
UBB	500648074101
UNSPSC	31161620
EAN	8717077201347
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M14
Length	65 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
DIN	960
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	40
b (min.): L200mm	53
b (min.): L≤125mm	34
d-D	M14
k	8.8
L (mm)	65
P	1.5
s	22

Technical Drawing

