



Small hexagon head set screw with full dog point DIN 561 Steel Plain 22H M10X35

Article number	01098.100.035
Brand	-
UBB	952351213998
UNSPSC	31161620
EAN	8715492022707
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	35 mm
Threaded pitch (P)	1.5
Class	22H
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Point	Dog
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	561
NF	E25-133

Technical Specification

d-D	M10
dp (max.)	7
k	7
L (mm)	35
P	1.5
s	13
z2 (min.)	5

Technical Drawing

