



## Small hexagon head set screw with full dog point DIN 561 Steel Plain 22H M10X50

|                |               |
|----------------|---------------|
| Article number | 01098.100.050 |
| Brand          | -             |
| UBB            | 952351214152  |
| UNSPSC         | 31161620      |
| EAN            | 8715492022721 |
| PKG. of 100    | Full Box Only |

### Technical Parameters

|                    |               |
|--------------------|---------------|
| Diameter           | M10           |
| Length             | 50 mm         |
| Threaded pitch (P) | 1.5           |
| Class              | 22H           |
| Driving features   | Hexagon       |
| Head shape         | Hexagon head  |
| Material           | Steel         |
| Thread direction   | Right         |
| Point              | Dog           |
| Surface treatment  | Plain         |
| Thread             | Metric thread |

### Standards

|     |         |
|-----|---------|
| DIN | 561     |
| NF  | E25-133 |

### Technical Specification

|           |     |
|-----------|-----|
| d-D       | M10 |
| dp (max.) | 7   |
| k         | 7   |
| L (mm)    | 50  |
| P         | 1.5 |
| s         | 13  |
| z2 (min.) | 5   |

### Technical Drawing

