



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M3X30

Article number	01200.030.030
Brand	-
UBB	500644996224
UNSPSC	31161620
EAN	8717077049277
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): L≤125mm	12
d-D	M3
k	2
L (mm)	30
P	0.5
s	5.5

Technical Drawing

