



Hexagon head bolt ISO 4014
Steel Zinc plated 8.8 M4X40

Article number	01200.040.040
Brand	-
UBB	950351140401
UNSPSC	31161620
EAN	8715492024688
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NEN	1555
NF	E25-112

Technical Specification

b (min.): L≤125mm	14
d-D	M4
k	2.8
L (mm)	40
P	0.7
s	7

Technical Drawing

