



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M5X40

Article number	01200.050.040
Brand	-
UBB	950351140815
UNSPSC	31161620
EAN	8715492024770
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	40
P	0.8
s	8

Technical Drawing

