



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M6X110

Article number	01200.060.110
Brand	-
UBB	950351142894
UNSPSC	31161620
EAN	8715492025036
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M6
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
ISO	4014
DIN	931
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	110
P	1
s	10

Technical Drawing

