



Hexagon head bolt DIN 931 Steel Zinc plated 8.8 M12X80/S=19

Article number	01200.120.080
Brand	-
UBB	950351148677
UNSPSC	31161620
EAN	8715492025975
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	80 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
ASME	B18.2.3.1M
DIN	931
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	80
P	1.75
s	19

Technical Drawing

