



## Hexagon head bolt DIN 931 Steel Zinc plated 8.8 M12X150/S=19

|                |               |
|----------------|---------------|
| Article number | 01200.120.150 |
| Brand          | -             |
| UBB            | 950351149337  |
| UNSPSC         | 31161620      |
| EAN            | 8715492026101 |
| PKG. of 50     | Full Box Only |

### Technical Parameters

|                   |               |
|-------------------|---------------|
| Diameter          | M12           |
| Length            | 150 mm        |
| Class             | 8.8           |
| Driving features  | Hexagon       |
| Head shape        | Hexagon head  |
| Material          | Steel         |
| Thread direction  | Right         |
| Surface treatment | Zinc plated   |
| Thread            | Metric thread |

### Standards

|      |            |
|------|------------|
| DIN  | 931        |
| NEN  | 1555       |
| ASME | B18.2.3.1M |
| NF   | E25-112    |
| ISO  | 4014       |

### Technical Specification

|                           |      |
|---------------------------|------|
| b (min.):<br>125mmL≤200mm | 36   |
| b (min.): L200mm          | 49   |
| b (min.): L≤125mm         | 30   |
| d-D                       | M12  |
| k                         | 7.5  |
| L (mm)                    | 150  |
| P                         | 1.75 |
| s                         | 19   |

### Technical Drawing

