



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M20X160

Article number	01200.200.160
Brand	-
UBB	950351157082
UNSPSC	31161620
EAN	8715492027238
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	160 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
NEN	1555
DIN	931
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200$ mm	52
b (min.): $L \geq 200$ mm	65
b (min.): $L \leq 125$ mm	46
d-D	M20
k	12.5
L (mm)	160
P	2.5
s	30

Technical Drawing

