



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M20X440

Article number	01200.200.440
Brand	-
UBB	500644630997
UNSPSC	31161620
EAN	8717077011984
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	440 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1555
ISO	4014
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	52
b (min.): $L \geq 200$ mm	65
b (min.): $L \leq 125$ mm	46
d-D	M20
k	12.5
L (mm)	440
P	2.5
s	30

Technical Drawing

