



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M39X190

Article number	01200.390.190
Brand	-
UBB	500644636366
UNSPSC	31161620
EAN	8717077012523
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M39
Length	190 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112
DIN	931

Technical Specification

b (min.): 125mm $L \leq 200$ mm	90
b (min.): $L \geq 200$ mm	103
b (min.): $L \leq 125$ mm	84
d-D	M39
k	25
L (mm)	190
P	4
s	60

Technical Drawing

