



Hexagon head bolt ISO 4014 Steel Zinc plated 8.8 M42X120

Article number	01200.420.120
Brand	-
UBB	500501785520
UNSPSC	31161620
EAN	8715494227377
PKG. of 1	Full Box Only

Technical Parameters

Diameter	M42
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	96
b (min.): L200mm	109
b (min.): L≤125mm	90
d-D	M42
k	26
L (mm)	120
P	4.5
s	65

Technical Drawing

