

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M4X25

Article number	01220.040.025
Brand	-
UBB	954351119761
UNSPSC	31161620
EAN	8715492032904
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M4
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1555
NF	E25-112
ISO	4014
DIN	931

Technical Specification

b (min.): L≤125mm	14
d-D	M4
k	2.8
L (mm)	25
P	0.7
s	7

Technical Drawing

