

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M5X30

Article number	01220.050.030
Brand	-
UBB	952351328184
UNSPSC	31161620
EAN	8715492032966
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
NEN	1555
ISO	4014
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	30
P	0.8
s	8

Technical Drawing

