

Hexagon head bolt ISO 4014 Steel Zinc plated yellow passivated 8.8 M8X110

Article number	01220.080.110
Brand	-
UBB	952351328341
UNSPSC	31161620
EAN	8715492033369
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	110 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22
d-D	M8
k	5.3
L (mm)	110
P	1.25
s	13

Technical Drawing

