

Hexagon head bolt DIN 931 Steel Zinc plated yellow passivated 8.8 M10X40/S=17

Article number	01220.100.040
Brand	-
UBB	950351168139
UNSPSC	31161620
EAN	8715492033475
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

DIN	931
ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	40
P	1.5
s	17

Technical Drawing

