

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M5X40

Article number	01224.050.040
Brand	-
UBB	500648268323
UNSPSC	31161620
EAN	8717077232495
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M5
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NF	E25-112
NEN	1555
ISO	4014
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	22
b (min.): L≤125mm	16
d-D	M5
k	3.5
L (mm)	40
P	0.8
s	8

Technical Drawing

