

## Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M5X45



Article number 01224.050.045

Brand -

UBB 500648268406

UNSPSC 31161620

EAN 8717077232501

PKG. of 200 Full Box Only

### Technical Parameters

Diameter (d-D)	M5
Length (L) (mm)	45
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III) passivation
Thread	Metric thread

### Standards

ASME	B18.2.3.1M
DIN	931
NF	E25-112
ISO	4014

### Technical Specification

b (min.): 125mm <math>L \leq 200\text{mm}</math>	22
b (min.): $L \leq 125\text{mm}$	16
k	3.5
P	0.80
s	8

### Technical Drawing

