

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M6X40



| | |
|----------------|---------------|
| Article number | 01224.060.040 |
| Brand | - |
| UBB | 500648268810 |
| UNSPSC | 31161620 |
| EAN | 8717077232549 |
| PKG. of 200 | Full Box Only |

Technical Parameters

| | |
|-------------------|---|
| Diameter (d-D) | M6 |
| Length (L) (mm) | 40 |
| Class | 8.8 |
| Driving features | Hexagon |
| Head shape | Hexagon head |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated with thick Cr(III) passivation |
| Thread | Metric thread |

Standards

| | |
|------|------------|
| ISO | 4014 |
| DIN | 931 |
| ASME | B18.2.3.1M |
| NF | E25-112 |

Technical Specification

| | |
|---|----|
| b (min.): 125mm $L \leq 200\text{mm}$ | 24 |
| b (min.): $L \leq 125\text{mm}$ | 18 |
| k | 4 |
| P | 1 |
| s | 10 |

Technical Drawing

