

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M6X50



Article number	01224.060.050
Brand	-
UBB	500648269073
UNSPSC	31161620
EAN	8717077232563
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	50
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III) passivation
Thread	Metric thread

Standards

DIN	931
NF	E25-112
ISO	4014
ASME	B18.2.3.1M

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	24
b (min.): $L \leq 125\text{mm}$	18
k	4
P	1
s	10

Technical Drawing

