

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M6X55



Article number	01224.060.055
Brand	-
UBB	500648269156
UNSPSC	31161620
EAN	8717077232570
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M6
Length (L) (mm)	55
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III) passivation
Thread	Metric thread

Standards

ISO	4014
DIN	931
ASME	B18.2.3.1M
NF	E25-112

Technical Specification

b (min.): 125mm $L \leq 200\text{mm}$	24
b (min.): $L \leq 125\text{mm}$	18
k	4
P	1
s	10

Technical Drawing

