

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M6X60

Article number	01224.060.060
Brand	-
UBB	500648269230
UNSPSC	31161620
EAN	8717077232587
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

NEN	1555
ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

Technical Specification

b (min.): 125mmL≤200mm	24
b (min.): L≤125mm	18
d-D	M6
k	4
L (mm)	60
P	1
s	10

Technical Drawing

