

## Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M20X75

|                |               |
|----------------|---------------|
| Article number | 01224.200.075 |
| Brand          | -             |
| UBB            | 500648277316  |
| UNSPSC         | 31161620      |
| EAN            | 8717077233393 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                   |                                             |
|-------------------|---------------------------------------------|
| Diameter          | M20                                         |
| Length            | 75 mm                                       |
| Class             | 8.8                                         |
| Driving features  | Hexagon                                     |
| Head shape        | Hexagon head                                |
| Material          | Steel                                       |
| Thread direction  | Right                                       |
| Surface treatment | Zinc plated with thick Cr(III+) passivation |
| Thread            | Metric thread                               |

### Standards

|      |            |
|------|------------|
| NF   | E25-112    |
| DIN  | 931        |
| ISO  | 4014       |
| NEN  | 1555       |
| ASME | B18.2.3.1M |

### Technical Specification

|                           |      |
|---------------------------|------|
| b (min.):<br>125mmL≤200mm | 52   |
| b (min.): L200mm          | 65   |
| b (min.): L≤125mm         | 46   |
| d-D                       | M20  |
| k                         | 12.5 |
| L (mm)                    | 75   |
| P                         | 2.5  |
| s                         | 30   |

### Technical Drawing

