

Hexagon head bolt ISO 4014 Steel Zinc plated with thick Cr(III) passivation 8.8 M20X100



Article number	01224.200.100
Brand	-
UBB	500648277563
UNSPSC	31161620
EAN	8717077233416
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M20
Length (L) (mm)	100
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III) passivation
Thread	Metric thread

Standards

NF	E25-112
DIN	931
ASME	B18.2.3.1M
ISO	4014

Technical Specification

b (min.): 125mm<L≤200mm	52
b (min.): L>200mm	65
b (min.): L≤125mm	46
k	12.5
P	2.50
s	30

Technical Drawing

