

Hexagon head screw ISO 4017 Steel Zinc plated yellow passivated 8.8 M3X10

Article number	01230.030.010
Brand	-
UBB	952351982980
UNSPSC	31161620
EAN	8715492035721
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	10 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

NEN	1568
NF	E25-114
ASME	B18.2.3.1M
DIN	933
ISO	4017

Technical Specification

d-D	M3
k	2
L (mm)	10
P	0.5
s	5.5

Technical Drawing

