

Hexagon head screw ISO 4017 Steel Zinc plated yellow passivated 8.8 M3X20

Article number	01230.030.020
Brand	-
UBB	953351863832
UNSPSC	31161620
EAN	8715492035752
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	20 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	933
NF	E25-114
ISO	4017
NEN	1568

Technical Specification

d-D	M3
k	2
L (mm)	20
P	0.5
s	5.5

Technical Drawing

