

Hexagon head screw ISO 4017 Steel Zinc plated yellow passivated 8.8 M3X25

Article number	01230.030.025
Brand	-
UBB	953351863915
UNSPSC	31161620
EAN	8715492035769
PKG. of 500	Full Box Only

Technical Parameters

Diameter	M3
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Standards

ASME	B18.2.3.1M
NEN	1568
ISO	4017
NF	E25-114
DIN	933

Technical Specification

d-D	M3
k	2
L (mm)	25
P	0.5
s	5.5

Technical Drawing

