

Hexagon head screw ISO 4017 Steel Zinc plated with thick Cr(III) passivation 8.8 M10X12

Article number	01237.100.012
Brand	-
UBB	500648285491
UNSPSC	31161620
EAN	8717077234208
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M10
Length	12 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

ASME	B18.2.3.1M
DIN	933
NEN	1568
NF	E25-114
ISO	4017

Technical Specification

d-D	M10
k	6.4
L (mm)	12
P	1.5
s	16

Technical Drawing

