



Hexagon head bolt MF DIN 960 Steel Zinc plated yellow passivated 8.8 M10X1,25X40/S=17

Article number	01240.100.040
Brand	-
UBB	951351589399
UNSPSC	31161620
EAN	8715492039033
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric fine thread

Standards

ISO	8765
NF	E25-152
NEN	1555
DIN	960

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45
b (min.): L≤125mm	26
d-D	M10
k	6.4
L (mm)	40
P	1.25
s	17

Technical Drawing

