



Hexagon head bolt MEF DIN 960 Steel Zinc plated yellow passivated 8.8 M12X1,25X60/ S=19

Article number	01241.120.060
Brand	-
UBB	951351590934
UNSPSC	31161620
EAN	8715492039590
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric extra fine thread

Standards

DIN	960
NEN	1555
ISO	8765
NF	E25-152

Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49
b (min.): L≤125mm	30
d-D	M12
k	7.5
L (mm)	60
P	1.25
s	19

Technical Drawing

