



Hexagon flange bolt DIN 6921 Steel Zinc plated yellow passivated 8.8 M12X90

Article number	01256.120.090
Brand	-
UBB	952351234457
UNSPSC	31161620
EAN	8715492040985
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M12
Length	90 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric thread

Info

Specific features of hexagon bolts with flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

EN	≈1665
ISO	≈4162
ASME	≈B18.2.3.4M
DIN	6921

b (min.)	30
d-D	M12
dc (max.)	26.6
k (max.)	11.5
L (mm)	90
P	1.75
s	16

