



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Steel Zinc plated 8.8 M6X16**

Article number	01258.060.016
Brand	-
UBB	954351276009
UNSPSC	31161620
EAN	8715492041289
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	16 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

DIN	≈6921
ISO	≈4162
EN	≈1665
ASME	≈B18.2.3.4M

Technical Specification

b (min.)	18
d-D	M6
dc (max.)	14.2
k (max.)	6.6
L (mm)	16
P	1
s	10

Technical Drawing

