



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Steel Zinc plated 8.8 M6X30**

Article number	01258.060.030
Brand	-
UBB	954351276348
UNSPSC	31161620
EAN	8715492041319
PKG. of 200	Full Box Only

Technical Parameters

Diameter	M6
Length	30 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info

Specific features of hexagon bolts with serrated flange: The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure. The serrated flange rim gives excellent self-locking properties. Large (oversized) holes and/or tooling holes can be covered by the flange. Washers are not necessary.

Standards

ASME	≈B18.2.3.4M
DIN	≈6921
EN	≈1665
ISO	≈4162

Technical Specification

b (min.)	18
d-D	M6
dc (max.)	14.2
k (max.)	6.6
L (mm)	30
P	1
s	10

Technical Drawing

