



**Hexagon flange bolt with  
serrated flange, DIN ≈6921  
Steel Zinc plated 8.8 M8X25**

Article number	01258.080.025
Brand	-
UBB	954351276678
UNSPSC	31161620
EAN	8715492041340
PKG. of 200	Full Box Only

**Technical Parameters**

Diameter	M8
Length	25 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info      Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

**Standards**

DIN	≈6921
ISO	≈4162
ASME	≈B18.2.3.4M
EN	≈1665

Technical Specification

d-D	M8
dc (max.)	18
k (max.)	8.1
L (mm)	25
P	1.25
s	13

Technical Drawing

