



**Hexagon flange bolt with
serrated flange, DIN ≈6921
Steel Zinc plated 8.8 M10X35**

Article number	01258.100.035
Brand	-
UBB	954351277338
UNSPSC	31161620
EAN	8715492041418
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M10
Length	35 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Info Specific features of hexagon bolts with serrated flange:The flange enables built up forces under the bolt head to be spread over a larger area, consequently resulting in lower surface pressure.The serrated flange rim gives excellent self-locking properties.Large (oversized) holes and/or tooling holes can be covered by the flange.Washers are not necessary.

Standards

ASME	≈B18.2.3.4M
DIN	≈6921
ISO	≈4162
EN	≈1665

Technical Specification

d-D	M10
dc (max.)	22.3
k (max.)	9.2
L (mm)	35
P	1.5
s	15

Technical Drawing

