



## Hexagon nut DIN 934 Steel Zinc plated |8| M10

Article No.	01300.100.001
Brand	-
UBB	950355012531
UNSPSC	31161727
EAN	8715492042101
PKG. of 250	Full Box Only

### Technical Parameters

Diameter (d-D)	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	934
NEN	1560
NF	E25-401

### Technical Specification

m	8
P	1.50
s	17

### Technical Drawing

