

## Hexagon nut DIN 934 Steel Zinc plated yellow passivated |8| M18

|                |               |
|----------------|---------------|
| Article number | 01320.180.001 |
| Brand          | -             |
| UBB            | 950355018579  |
| UNSPSC         | 31161727      |
| EAN            | 8715492042927 |
| PKG. of 50     | Full Box Only |

### Technical Parameters

|                   |                                  |
|-------------------|----------------------------------|
| Diameter          | M18                              |
| Class             | 8                                |
| Driving features  | Hexagon                          |
| Material          | Steel                            |
| Thread direction  | Right                            |
| Surface treatment | Zinc plated yellow<br>passivated |
| Thread            | Metric thread                    |

### Standards

|     |         |
|-----|---------|
| NF  | E25-401 |
| NEN | 1560    |
| DIN | 934     |

### Technical Specification

|     |     |
|-----|-----|
| d-D | M18 |
| m   | 15  |
| P   | 2.5 |
| s   | 27  |

### Technical Drawing

