

Hexagon nut DIN 934 Steel Zinc plated with thick Cr(III) passivation |8| M5

Article number	01325.050.001
Brand	-
UBB	500505355619
UNSPSC	31161727
EAN	8715494207898
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M5
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated with thick Cr(III+) passivation
Thread	Metric thread

Standards

DIN	934
NF	E25-401
NEN	1560

Technical Specification

d-D	M5
m	4
P	0.8
s	8

Technical Drawing

