

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M8X40

Article number	01400.080.040
Brand	-
UBB	950351187022
UNSPSC	31161620
EAN	8715492408075
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Length	40 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ISO	4014
ASME	B18.2.3.1M
NF	E25-112
NEN	1555
DIN	931

Technical Specification

b (min.): 125mmL≤200mm	28
b (min.): L≤125mm	22

Technical Drawing

d-D	M8
k	5.3
L (mm)	40
P	1.25
s	13

FABORY

