

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M10X120

Article number	01400.100.121
Brand	-
UBB	952351097821
UNSPSC	31161620
EAN	8715492408341
PKG. of 50	Full Box Only

Technical Parameters

Diameter	M10
Length	120 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

Standards

ASME	B18.2.3.1M
NEN	1555
NF	E25-112
DIN	931
ISO	4014

Technical Specification

b (min.): 125mmL≤200mm	32
b (min.): L200mm	45

Technical Drawing

b (min.): $L \leq 125\text{mm}$	26
d-D	M10
k	6.4
L (mm)	120
P	1.5
s	16

