

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M12X140/S=19

Article number	01400.120.140
Brand	-
UBB	950351191552
UNSPSC	31161620
EAN	8715492408600
PKG. of 25	Full Box Only

### Technical Parameters

Diameter	M12
Length	140 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

DIN	931
ISO	4014
NEN	1555
ASME	B18.2.3.1M
NF	E25-112

### Technical Specification

b (min.): 125mmL≤200mm	36
b (min.): L200mm	49

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	30
d-D	M12
k	7.5
L (mm)	140
P	1.75
s	19

