

Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M12X180/S=19



Article No.	01400.120.180
Brand	-
UBB	950351938127
UNSPSC	31161620
EAN	8715492408631
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Length (L) (mm)	180
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Wrench width	19

Standards

NF	E25-112
ASME	B18.2.3.1M
DIN	931
NEN	1555
ISO	4014

Info
 ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

Technical Specification

b (min.): L≤125mm 30

Technical Drawing

s 19

b (min.): 36
125mm < L ≤ 200mm

IN FASTENING SOLUTIONS

k 7.5

b (min.): L > 200mm 49

P 1.75

