

## Hexagon head bolt ISO metric thread DIN 931 Steel Hot dip galvanized 8.8 M16X60

Article number	01400.160.060
Brand	-
UBB	950351191891
UNSPSC	31161620
EAN	8715492408662
PKG. of 25	Full Box Only

### Technical Parameters

Diameter	M16
Length	60 mm
Class	8.8
Driving features	Hexagon
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info  
ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H. ISO metric

### Standards

NEN	1555
ASME	B18.2.3.1M
DIN	931
ISO	4014
NF	E25-112

### Technical Specification

b (min.): 125mmL≤200mm	44
b (min.): L200mm	57

### Technical Drawing

b (min.): $L \leq 125\text{mm}$	38
d-D	M16
k	10
L (mm)	60
P	2
s	24

