


Hexagon head bolt ISO metric thread ISO 4014 Steel Hot dip galvanized 8.8 M16X160



Article No.	01400.160.160
Brand	-
UBB	950351938382
UNSPSC	31161620
EAN	8715492408785
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M16
Length (L) (mm)	160
Class	8.8
Driving features	Hexagon
Extra info	ISO metric
Head shape	Hexagon head
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized bolts and screws are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.

Standards

DIN	931
NF	E25-112
ASME	B18.2.3.1M
ISO	4014
NEN	1555

Technical Specification

b (min.):	44
125mm<L≤200mm	

Technical Drawing

b (min.): $L \leq 125\text{mm}$ 38

s 24

PURVISOR
SETTING THE STANDARD
IN FASTENING SOLUTIONS
2

b (min.): $L > 200\text{mm}$ 57

k 10

